

ANATASE

518-24-VGL

FINISHES

VINTAGE GOLD LEAF

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 24.25"

Width/Diameter: 24"

Minimum Height: 34.75"

Maximum Height: 105.25"

Canopy/Backplate: 6.75"

Hanging Type: 72" Chain

Product Weight: 35.2lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Cast Glass

Shade 1 Finish: Remolino Blanco with Light
Smoke

Shade 1 Top Width: 4.75"

Shade 1 Height: 13.5"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: B11

Max Wattage: 10

Bulb Quantity: 5

Bulb Included: No

Wire Length: 144"

Cord Type: SPT-1 SILVER W/ TINNED GROUND
WIRE

Gem Box Required (2"x3"):

Dark Sky: No

SHIPPING

Carton 1: 32" x 32" x 24"

Carton 1 Weight: 77lb

Shipping Method: Truck Only

Country of Origin: PH

