Rune | E30134-24BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Artisanal cast glass slabs are supported by a Die Cast Aluminum bracket finished in an outdoor rated Black powder coat. Emphasizing the unique beauty of the glasses' imperfect contours, the sconces accentuate these features with concealed LED lighting. Available in 3 size configurations, the sconces provide adequate lighting and showcase the craftsmanship of the artistic glass.



MEASUREMENTS

DIMENSION	: 5.25" W x 15.5" H x 2" Ext
BACK PLATE	: 4.75" W x 4.75" H x 5.9" HCO
HANGING WEIGHT	: 6.66 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 1,200 Rated (690 Del.)
BULB	: 2 x 8W LED PCB Integrated , 16W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: N
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Up

FINISHES OPTION

Black (BK)

GLASS

Clear 24

MATERIAL

Aluminum

RATINGS

cETLus
Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Up/Down
RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com