

KASPARS

B7910-TBK/SBK

Influenced by utilitarian Scandinavian design, Kaspars provides a depth that moves beyond minimalism. The familiar RLM silhouette is elevated by faceted sides and a layered chimney punctuated by circular perforations. With a Textured Black and Soft Black exterior and Soft White interior, the mix of finishes elevates the sleek silhouette. Capable of illuminating large spaces, this Dark Sky-rated 1-light sconce is available in two sizes.

FINISHES

TEXTURE BLACK w/ SOFT BLACK

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 9.75"

Width/Diameter: 12.5"

Canopy/Backplate: 5"

Product Weight: 3lb

Extension: 20.25"

Top to Center: 2.75"

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Metal

Shade 1 Finish: Soft Black

Shade 1 Top Width: 7.5"

Shade 1 Bottom L/W: 0" / 12.5"

Shade 1 Height: 3.5"



ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: A19

Max Wattage: 15

Bulb Quantity: 1

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 18" x 16" x 10"

Carton 1 Weight: 6lb

Shipping Method: Ground

Country of Origin: VN