

DANAE

H1107301-PN

Inspired by the beauty of Orrefors vases, the Danae family pairs clean-cut metalwork with distinctive fluted glass. This petite bath sconce features a dense, scalloped glass shade that catches and scatters the glow within. Available with 1, 2, or 3 lights, and finished in Aged Brass or Polished Nickel, Danae is fresh, yet functional for a powder room or bath.

FINISHES

POLISHED NICKEL

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 6.25"

Width/Diameter: 4.25"

Length: 5"

Canopy/Backplate: 4.25"

Product Weight: 2lb

Extension: 5"

Top to Center: 4"

Canopy/Backplate Shape: Rectangle

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: Clear Optic

Shade 1 Top Width: 4"

Shade 1 Height: 4.5"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: B11

Max Wattage: 10

Bulb Quantity: 1

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 8" x 7" x 10"

Carton 1 Weight: 4lb

Shipping Method: Ground

Country of Origin: VN

