Phoenix | E11392-GYBK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Both modern and industrial, the angular lines of these aluminum spun shades refresh a classic concept in a clean, contemporary execution. The shades - available in Brick, Black, and a Pale Gray powder coated finish, feature multiple joints and peaks in their form and at their bottom intentionally return inward. The shape at the bottom is not only attractive, but a cleverly conceived method to support a wire network of Black steel that forms a cage without visible hardware. Illuminated from within the spun metal shades in 3 varying sizes and shapes, the LED lamp provided shines light below and disperses through the wireway creating a beautiful radiating light pattern.



MEASUREMENTS

DIMENSION	: 15.75" W x 19" H x 15.75" Ext
MAX OAH	: 142.25" OAH
CANOPY	: 4.75" W x 0.25" H x 4.75" L
HANGING WEIGHT	: 6.9 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 900 Rated (650 Del.)
BULB	: 1 x 9W LED E26 Medium , 9W Total
BULB INCLUDED	: (Included)
DIMMABLE	:
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

- Black / Gold (BKGLD)
- Brick/Black (BRKBK)
- Gray / Black (GYBK)

MATERIAL

Alumimum, Steel

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com