
Vanish | E24837-75AL

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

A disappearing act of LED along an extended length of crystal-clear acrylic, these pendants vanish from view and simultaneously guide the slim, streamlined LED light source. Twist the machined aluminum ends finished in Gunmetal or Brushed Aluminum to direct the light wherever you choose.



MEASUREMENTS

DIMENSION	: 72" L x 2" W x 2" H
MAX OAH	: 124" OAH
CANOPY	: 6" W x 2" H x 6" L
HANGING WEIGHT	: 9 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 1,920 Rated (1,850 Del.)
BULB	: 2 x 12W LED DC Integrated , 24W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 85 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Brushed Aluminum (AL)

Gunmetal (GM)

GLASS

Clear Acrylic 75

MATERIAL

Steel, Aluminum, Acrylic

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com