Tartan | E24811-82PC

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Inspired by patterned fabrics of the Scottish Highlands, the Tartan collection features a waving grid-like design etched deep into the transparent acrylic body. Hand-formed into a curling structure, the material gives the impression of billowing in the breeze. Color temperature selection at the canopy allows you to choose from Warm, Neutral, and Cool White colored LED lighting.



MEASUREMENTS

DIMENSION	: 15" W x 13" H x 10" Ext
MAX OAH	: 5" W x 5" H
HANGING WEIGHT	: 5.28 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 1,040 Rated (650 Del.)
BULB	: 1 x 13W LED DC Integrated , 13W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 30-35-40K
LIGHTING_DIRECTION	: All

FINISHES OPTION

Brushed Champagne (BCN)

Polished Chrome (PC)

GLASS

Heavy Faceted 82

MATERIAL

Stainless Steel, Acrylic

RATINGS

cETLus
Damp Location

ADDITIONAL

INSTALL UP/DOWN: Down
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com