



QRP® Qualatherm®

Heat & Cold Resistant Glove with Silicone Rubber Outer Shell and Nylon Lining - 12"

- Packaged for Class 100 (ISO5/M3.5) applications
- Wet or dry contact temperatures from -78F to 392F (-61.4C to 200C)
- PolyTuff silicone elastomer is sulfur-free. Excellent resistance to chemicals, solder and fluxes
- RoHS Compliant



Technical Data

Color	White
Sizes Available	M-XL
Packaging	Case
Packed	1 Pair/Case
Case Dimensions (in)	11.00 x 6.00 x 5.00
Case Weight (lbs)	0.99
Country of Origin	Japan
Polymer	Silicone
Grip	Smooth
Cuff	Open
Length	12"
Construction	Supported
Certifications	TAA Compliant

Performance Data

ISO Cleanroom	ISO 5 (Class 100)
Temperature Resistant	Extreme Cold

Care Instructions



Machine Wash



Water Temp 40°C



Do Not Bleach



Hang Dry

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
70GM	White	M	616314279102	10616314279109	20616314279106
70GL	White	L	616314279096	10616314279093	20616314279090
70GXL	White	XL	616314279119	10616314279116	20616314279113