Project Name

Location

Prepared By



SATCO S3385

40W TORP CAND FR 220V.

Notes

[www] 09-27-2021 00:19:12

General	
Status	Active
Watts	40W
Volts	220V
Shape	B10
Lumens	330L
Base	Candelabra
Filament	CC-2F
ANSI Base	E12
Finish	Frost
CCT (Kelvin)	2700
Temperature	Warm White
CRI	100
Beam Spread	360
Dimmable	Yes-Dimmable
Hours Rated	1000
Lamp Type	Candle
Technology	Incandescent

Physical	
MOL	3.75
MOD	1.25

Additional Information	
Warranty	Avg. Rated Hour Limited

Compliance	
Energy Star	No
California Status	Non-Compliant
RoHS Compliant	Yes
SDS Sheet	Incandescent_Lamp

Copyright 2020 Satco Products, Inc.
All Rights Reserved

For More Information Visit:
http://www.satco.com/