trumeter
innovation by design

VISTA TOUCH FLOW

Touch Screen Flow Rate Indicator and Totalizer

THREE YEAR 3 WARRANTY

For use with Industrial Flow Meters

NOW WITH DATA LOGGING



MULTIPLE CONFIGURABLE DISPLAY OPTIONS



trumetercloud



- Built-in Gauges — For different requirements
- Modbus® — RTU over RS485 and TCP over Ethernet
- Graphic Display — 65k DISPLAY
- Touchscreen programmable
- Built-in remote monitoring — trumetercloud READY
- Data logging and load/save configurations via USB flash drive
- 2 Relay Outputs, 1 Analog Output, 2 Digital Inputs
- 0.1% Accuracy
- Secure API access

- 2 independent resettable totalizers
- Scalable timebase – min, seconds, hours
- Scalable unit of measure – liters, gallons (US/UK), fluid oz (US/UK), cubic feet, cubit meters
- 0.1% accuracy across the input range
- Local data logging through USB
- 65K full color 70mm x 70mm [2.76" x 2.76"] graphics display
- Simple and intuitive touchscreen
- Fully configurable from the front panel
- Load and save configuration data to a USB flash drive
- Free access to the IoT Trumeter Cloud remote monitoring texts and emails alarm notifications
- Modbus® RTU and TCP
- Industry standard ¼ DIN mounting
- Ethernet and RS485 as standard
- Modular pluggable quick connect/disconnect connectors
- IP65, NEMA250 & UL50E Type 12 and Type 4 protection
- API access for secure, read-only device data for use in other systems, dashboards, or reports.

Go to www.trumeter.com for further information

trumeter
innovation by design

custom is our passion

Measurement Input

Input	Operating Range	Accuracy	Resolution	Frequency
Voltage	0V to +10V DC	0.1% of full scale	400uV	DC
Current	-50mA to +50mA	0.1% of full scale	2uA	DC
Pulse / Rate	Logic 0 = 0 to 0.6V DC Logic 1 = 2.5V to 24V DC	100PPM	1uSec	0 to 10KHz
		Pulse input supports (NPN or PNP), digital logic (logic 0 <0.6V; logic 1 2.5V-24V), and zero volt contact closure		

Power Supply

Mains Version	100-277VAC 50/60Hz 10W
Low Voltage Version	12-24VAC/DC and 50/60Hz 10W

Memory

2MB of internal non-volatile memory to store all settings. Supports USB flash drive (FAT16/FAT32 format up to 32GB).

Communications, Networking and IoT

RS485	Modbus RTU
Ethernet	Modbus TCP
Platform	Trumeter IoT Cloud
USB	Mass storage (USB flash drive)

Outputs

Relay	2 x Form C relay (277V AC / 5A Max | 30V DC / 5A Max)
Analog	4-20mA Analog Output
24VDC	Excitation voltage output (50mA Max)

Control Inputs

Opto Isolated	2 x control input (12V to 277V AC/DC)

Certifications

CE, UL and cUL, EN61010-1


Environmental

Operating Temperature	-20°C to +60°C (-4°F to +140°F)
Storage temperature	-20°C to +70°C (-4°F to +158°F)
Humidity	1% to 85% max non-condensing
IP rating (from the front)	IP65, UL50E Type 4 & Type 12, NEMA250 Type 4 & Type 12
Shock	20g to IEC68-2-27
Vibration	5-500Hz, 2g
Altitude	up to 2000 meters
Installation Category	II
Pollution Degree	2


Display


Visible screen area	70mm x 70mm [2.76" x 2.76"]
Resolution	480 x 480 pixels
Brightness	450cd/m²
Contrast ratio	800:1
Colors	65,536
Impact Resistance	IK03 Toughened glass to EN62262
Viewing angle	160° horizontally; 160° vertically
Touch	Multi zone touch capacitive
Scratch Resistance	6H to ASTM D4587

Typical Application



Mechanical





Cut Out: 92mm x 92mm (3.62 "x 3.62") as per DIN IEC 61554

Part Numbers

VT-FLOW-LV	Vista Touch Flow Meter 12-24VAC/DC
VT-FLOW-HV	Vista Touch Flow Meter 100-277VAC

c UL us LISTED
MEASURING AND TESTING EQUIPMENT
E469787

CE RoHS



www.trumeter.com

Trumeter (The Americas)
6601 Lyons Rd, Suite H-7
Coconut Creek, Florida
FL 33073,
USA
Tel: +1 954 725 6699
Email: sales.usa@trumeter.com

Trumeter (Europe)
Pilot Mill
Alfred Street
Bury,
BL9 9JR
Tel: +44 161 674 0960
Email: sales.uk@trumeter.com

Innovative Design Technologies Sdn. Bhd
Lot 5881, Lorong Iks Bukit Minyak 1
Taman Perindustrian Iks, 14000 Bukit Tengah
Penang, Malaysia
Web: www.idtworld.com
Tel: + 604 5015700
Email: sales.my@idtworld.com