Gravity | E42106-BKGLD

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

An elliptical shape in Gold finish is illuminated by dedicated LED lighting and secured to a disc in contrasting black finish making a modern silhouette rated for outdoor applications. Suitable for wet locations, the fixture is constructed of corrosive resistant aluminum channel finished in UV-rated outdoor powder coats and sealed within the frame to prevent water intrusion. With an extension less than 4 inches, this attractive sconce series is also inherently ADA compliant for indoor public spaces where needed.



MEASUREMENTS

DIMENSION	: 6" W x 18" H x 1.75" Ext
BACK PLATE	: 5.25" W x 5.25" H x 15.5" HCO
HANGING WEIGHT	: 2 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 670 Rated (450 Del.)
BULB	: 1 x 15W LED DC Integrated , 15W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac CL
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Directional

FINISHES OPTION

Black / Gold (BKGLD)

MATERIAL

Aluminum

RATINGS

cETLus
Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Any
RATED LIFE 30000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

PHOTOMETIC: Report Found Online

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com