Elysian | E11087-124NAB

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Segments of Clear glass cylinders are separated by distinctly rippled Clear crystal fonts on a thin Natural Aged Brass frame. The translucent segments are backlit with integrated LED illumination creating an airy, ethereal composition of glass textures. Available in vertical and horizontal configurations as well as sconce and portable configurations.



MEASUREMENTS

DIMENSION	: 7.75" L x 5.5" W x 22" H
HANGING WEIGHT	: 9.9 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 640 Rated (450 Del.)
BULB	: 1 x 8W LED AC Integrated , 8W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Natural Aged Brass (NAB)

GLASS

Ripple 124

MATERIAL

Steel, Aluminum, Glass

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com