



Enduring Quality, Exceptional Value

www.marathonbroadband.com

Wire Nuts

The Marathon Wire Nuts are winged or positive gripped, are UL/CSA listed as pressure-type wire connectors for use with copper-to-copper conductors, and come in a range of sizes and colors.

Common key features include:

- Thermoplastic flame-retardant shell
- Temperature rating up to 221° F
- Max voltage rating of 300V or 600V
- No pre-twisting required
- 3-year full warranty free from defects in design, materials, and workmanship



Part Number	UL/CSA Reference #	SIM	Box/Bag QTY	Color	For Use With	Description
WNP12TN500	P12C	40156499993	500	Tan	22-8 AWG	Tan, winged, twist on wire connector UL/CSA listed as a pressure-type wire connector. Wire connector is for use with copper-to-copper conductors with a max temp. rating of 221° F (105° C) and a max voltage rating of 600V. For use with 22-8 AWG wires. 500 count bag or 100 count box available.
WNP12TN100	P12C	40156499992	100			
WNP13RD500	P13	40156499990	500	Red	22-6 AWG	Red, winged, twist on wire connector UL/CSA listed as a pressure-type wire connector. Wire connector is for use with copper-to-copper conductors with a max temp. rating of 221° F (105° C) and a max voltage rating of 600V. For use with 22-6 AWG wires. 500 count bag or 100 count box available.
WNP13RD100	P13	40156499989	100			
WNP3OR500	P3	40156499984	500	Orange	22-14 AWG	Orange, positive grip, twist on wire connector UL/CSA listed as a pressure-type wire connector. Wire connector is for use with copper-to-copper conductors with a max temp. rating of 221° F (105° C) and a max voltage rating of 600V. For use with 22-14 AWG wires. 500 count bag or 100 count box available.
WNP3OR100	P3	40156499985	100			
WNP4YL500	P4	40156499982	500	Yellow	22-8 AWG	Yellow, positive grip, twist on wire connector UL/CSA listed as a pressure-type wire connector. Wire connector is for use with copper-to-copper conductors with a max temp. rating of 221° F (105° C) and a max voltage rating of 600V. For use with 22-8 AWG wires. 500 count bag or 100 count box available.
WNP4YL100	P4	40156499983	100			
WNP11YL100	P11V	40156499991	100	Yellow	22-8 AWG	Yellow, winged, twist on wire connector UL/CSA listed as a pressure-type wire connector. Wire connector is for use with copper-to-copper conductors with a max temp. rating of 221° F (105° C) and a max voltage rating of 600V. For use with 22-8 AWG wires. 100 count box available.
WNP1GR100	P1	40156499987	100	Grey	22-14 AWG	Gray, positive grip, twist on wire connector UL/CSA listed as a pressure-type wire connector. Wire connector is for use with copper-to-copper conductors with a max temp. rating of 221° F (105° C) and a max voltage rating of 300V. For use with 22-14 AWG wires. 100 count box available.
WNP2BL100	P2	40156499986	100	Blue	22-14 AWG	Blue, positive grip, twist on wire connector UL/CSA listed as a pressure-type wire connector. Wire connector is for use with copper-to-copper conductors with a max temp. rating of 221° F (105° C) and a max voltage rating of 300V. For use with 22-14 AWG wires. 100 count box available.
WNP6RD100	P6	40156499981	100	Red	22-10 AWG	Red, positive grip, twist on wire connector UL/CSA listed as a pressure-type wire connector. Wire connector is for use with copper-to-copper conductors with a max temp. rating of 221° F (105° C) and a max voltage rating of 600V. For use with 22-10 AWG wires. 100 count box available.
WNP17BL25	P17	40156499988	25	Blue	14-6 AWG	Blue, winged, twist on wire connector UL/CSA listed as a pressure-type wire connector. Wire connector is for use with copper-to-copper conductors with a max temp. rating of 221° F (105° C) and a max voltage rating of 600V. For use with 14-6 AWG wires. 25 count box available.

Marathon products are available from the following distributors:

Wesco
buy.wesco.com
866.746.3519

Anixter
Anixter.com
866.746.3519

221739D001
D230623-14