



EAN:	4013288111654	Size:	140x115x45 mm
Part number:	05104652001	Weight:	265 g
Article number:	848/851/867/19	Country of origin:	CZ
		Customs tariff number:	82079030

- Ideal for mobile repair and assembly work
- Rapidaptor holder for rapid bit change
- 1/4" drive suitable for power screwdrivers
- Rapidaptor universal holder, metal twist drill bits and bits with 1/4" drive
- In practical and robust belt pouch

19-piece metal twist drill bit and bit set. High quality metal twist drill bits for precise drilling in metal. Made out of high speed steel (HSS). A finely-tuned material elasticity provides for great durability. Very good concentricity. The hexagonal shaft ensures very good power transfer. Tough viscous bits for universal use. Drive: 1/4" hexagon, suitable for holders as per DIN ISO 1173-D 6.3. Includes robust belt pouch for secure storage.

Web link
<https://www.wera.de/en/05104652001>

Wera - 848/851/867/19
 05104652001 - 4013288111654

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

Twist drill bits for metal applications



Twist drill bits - for metal applications


- 1/4" drive suitable for holders as per DIN 3126-D 6.3 (ISO 1173)
- Hexagon shaft for very high torque transfer
- HSS = high speed steel with cone point
- Finely adjusted material elasticity for long service life
- Excellent concentricity
- Tough-absorbing tempered bits for particularly long service life

TZ-Bits



TZ-Bits are tough viscous bits with a torsion zone. Torsion bits absorb the damaging peak torque loads in the torsion zone. This prevents premature wear and enhances the service life of the bits.

Tough bits



Tough Wera bits prevent the tip from breaking prematurely. Z-bits usually are the bit for universal screwdriving applications.

Rapidaptor holder



Lightning-fast bit change without any extra tools. One-handed operation. With fast-rotating sleeve for easy wielding of the screwdriver.

Chuck-all




The Rapidaptor quick-release chucks hold 1/4" DIN ISO 1173-C 6,3 and E 6,3 as well as Wera series 1 and 4 bits.

Rapid-in and self-lock



The bit can be pushed into the adaptor without moving the sleeve. The lock is activated automatically as soon as the bit is applied to the screw. Bits are held securely and wobble-free.

Rapid-out



Simply push the sleeve forward to change the bit. The spring mechanism lifts the bit off the magnet and unlocks the tool. The bit can be easily removed. The rapid-out function makes it easy to remove even the smallest bits without extra tools.

Web link

<https://www.wera.de/en/05104652001>

Wera - 848/851/867/19
05104652001 - 4013288111654

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Set contents:

888/4/1 K Rapidaptor Universal Bit Holder, 1/4" x 50 mm



05052500001

1x 1/4" x 50 mm



848 HSS Metal Twist Drill Bits, 3 x 38 mm



05104610001

1x 3 x 38 mm

05104613001

1x 4 x 44 mm

05104615001

1x 4.2 x 45 mm

05104616001

1x 5 x 50 mm

05104618001

1x 6 x 50 mm

05104620001

1x 8 x 51 mm



851/1 TZ bits, PH 1 x 25 mm



05056505001

2x PH 1 x 25 mm

05056510001

3x PH 2 x 25 mm

05056525001

1x PH 3 x 25 mm



867/1 TORX® bits, TX 10 x 25 mm



05066485001

1x TX 10 x 25 mm

05066486001

1x TX 15 x 25 mm

05066487001

1x TX 20 x 25 mm

05066488001

1x TX 25 x 25 mm

05066490001

1x TX 30 x 25 mm

05066491001

1x TX 40 x 25 mm



Web link

<https://www.wera.de/en/05104652001>

Wera - 848/851/867/19

05104652001 - 4013288111654

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de