




TEGERA® 417

Learn more

QUALITY GLOVE THAT STAYS IN PLACE

Glove in high-quality synthetic leather, diamond pattern on the palm for a good grip. Double elastic around for a perfect fit. Soft, and provides excellent fingertip sensitivity for precision work with small materials, in both dry, wet, and cold environments.

CHARACTERISTICS

- Good fingertip sensitivity
- Flexible
- Durable
- Good fit
- Good grip
- Extra comfortable

FUNCTIONS

- Reinforced palm
- Soft

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Chrome allergy, Abrasion injuries, Blisters, Grazes, Scratches, lacerations, Contact with dirt, Drying out, Chapping, Contact with cold

PRIMARY ENVIRONMENTS OF USE

Dry environments, Cold environments, Dirty environments, Slippery environments

PRIMARY AREAS OF USE

Inspection work, Machine operating, Installation work, Machine driving, Warehouse work, Transport work

PRIMARY INDUSTRIES OF USE

Automotive repair and maintenance, Metal manufacturing and fabrication, Transport equipment manufacturing, Agriculture, forestry and fishing, Accommodation and food service (HoReCa), Facility management services, Machinery and equipment manufacturing, Automotive manufacturing, Transportation and logistics, Electricity and gas supply, Building and construction, Mining and quarrying, Warehousing, Public safety, security and defence, Retail and wholesale

TYPE OF WORK

Medium weight

SPECIFICATION

TYPE All-round work gloves, Assembly gloves, Cold insulation gloves
CATEGORY Cat. II
PALM MATERIAL Synthetic leather
BACK MATERIAL Polyester
LINING Fully lined
LINING MATERIAL Fleece
LENGTH 250-270 mm
DEXTERITY 3
COLOUR Grey
PAIRS PER: BUNDLE/CARTON 6/60
DISPLAY TYPE Hook with hangtag
FASTENING Elasticated 360°
INNER MATERIAL SPECIFICATION Polyester
OUTER MATERIAL SPECIFICATION Polyurethane, Polyester

COMPLIANCE

CE Cat. II
TP TC 019:2011

UKCA Cat. II
EN ISO 21420:2020

EAC

EN 388:2016+A1:2018 1121X

EN 511:2006 01X

ANSI 2 ABR

FEATURES

Warm lining

SIZE		ARTICLE NUMBER	EAN
8	M	417-8	7392626070004
9	L	417-9	7392626070028
10	XL	417-10	7392626069961
11	XXL	417-11	7392626069985

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.