



JSP® MK8 Evolution®

Type II Linesman Safety Helmet with HDPE Shell, EPS Impact Liner, Polyester Suspension, Wheel Ratchet Adjustment and 4-Point Chin Strap

- Mounted 4-point chin strap harness
- Chin strap ANSI approved for retention on Type II helmet
- Provides a secure fit in the most extreme conditions
- Meets ANSI/ISEA Z89.1, Type II, Class E requirements
- Offers Side (Lateral) Impact Protection which reduces the force of impact resulting from a blow which may be received off center as well as to the top of the head
- Also offers Side Penetration Protection in addition to crown penetration

Applications

- Mining
- Tunneling
- Demolition
- Utility Work
- Metalworking



Technical Data

Color	Yellow, White, Red, Blue
Sizes Available	OS
Packaging	Bagged Each
Packed	8/Case
Case Dimensions (in)	23.03 x 9.84 x 20.47
Case Weight (lbs)	17.17
Country of Origin	United Kingdom
Shell Material	HDPE
Shell	Non-Vented
Brim Style	Cap Style
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Suspension	Polyester Textile Straps
Chin Strap	4-Point Polyester
Sweatband	Microfiber
Size Range	53cm-63cm
Certifications	ANSI/ISEA Z89.1, TAA Compliant

Performance Data

ANSI Type	Type II
Electrical Class	Class E

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-AHS240-50	Blue	OS	5038428120371	5038428811019	5038428811019
280-AHS240-60	Red	OS	5038428749695	10616314800341	5038428749701
280-AHS240-10	White	OS	5038428120357	5038428810999	5038428810999
280-AHS240-20	Yellow	OS	05038428120364	5038428811002	05038428811002