



P65

Technical Data



Bouton® Optical Recon™

Rimless Safety Glasses with Translucent Brown Temple, I/O Blue Lens and Anti-Scratch / Anti-Fog Coating

- Lightweight, rimless design provides all day comfort
- Flexible bayonet temples contain rubber pads for a secure, non-slip fit
- Adjustable rubber nosepiece provides a comfortable fit
- 9 Base curve lens
- Meets ANSI Z87.1+
- Meets CSA Z94.3
- ⚠️ **WARNING:** Cancer and Reproductive Harm - www.P65Warnings.ca.gov

Color	Brown
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	23.62 x 14.76 x 16.73
Case Weight (lbs)	14.77
Country of Origin	Taiwan
Lens	Indoor Outdoor Blue
Frame Style	Rimless
Lens Color	Clear
Frame Fit	Universal
Lens Coating	Anti-Scratch, Anti-Fog
Bridge	Rubber
Temple	Bayonet, Rubber Tips
Base Curve	9
Certifications	ANSI Z87.1, CSA Z94.3 Certified, TAA Compliant, EN 166, EN 170, EN 172
Product Circularity	Recycled via Terracycle

Applications

- Artificial Light
- Indoor/Outdoor Work
- Fork Lift Operation

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-11

SKU Information

SKU	FRAME COLOR	LENS	LENS COLOR	LENS	UPC	UPC (INNER)	UPC (CASE)
				COATING			
250-32-0010	Clear	Clear	Clear	AS/AR	616314130298	01616314130297	02616314130296
250-32-0020	Clear	Clear	Clear	AS/AF	616314130274	01616314130273	02616314130272
250-32-0021	Black	Tinted	Gray	AS/AF	616314130281	01616314130280	02616314130289
250-32-0031	Black	Gradient	Clear	AS/AF	616314130311	01616314130310	02616314130319
250-32-0226	Brown	Indoor Outdoor Blue	Clear	AS/AF	616314130304	01616314130303	02616314130302
250-32-0520	Clear	Clear	Clear	AS/FL360	616314209529	01616314209528	02616314209527
250-32-0521	Black	Tinted	Gray	AS/FL360	616314209536	01616314209535	02616314209534
250-32-0551	Black	Tinted	Light Gray	FL360	616314249884	01616314249883	02616314249882

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated