



Technical Data

Color	Black
Sizes Available	OS
Packaging	Boxed
Packed	10/Case
Case Dimensions (in)	17.32 x 15.94 x 8.70
Case Weight (lbs)	10.47
Country of Origin	China
Hearing Style	Multi-Position
Protection Type	Passive
EN 352	EN352-1: Earmuffs (Passive)
Construction	Dielectric, Snap-In Cushions

Performance Data

NRR Rating (ANSI S3.19-1974)	30
SNR Rating	35
SLC 80 Class	Class

Howard Leight™ Verishield® 100

Dielectric Series - VS130M

Dielectric Passive Multi-Position Ear Muff - NRR 30

- Wider cup openings with snap-in replaceable memory-foam cushions for greater comfort and attenuation
- Neckband design allows clear head access for hard hats or welding helmets
- ABS molded oil-resistant cups with internal baffle design for lighter weight
- Air Flow Control™ technology allows for higher attenuation with smaller ear cups

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
1035187-VS	Black	OS	7312550351876		17312550351875