
5.Dangerous operation when fold the ladder: Do not put your hands on the pedals. Be careful not to be caught



This way will result in a b c as below:
a.very loud vibration and noise
b.hurt hand
c.bad mood

5.How to install the hooks



6.The movement and storage of the ladder



1.The ladder is flexible and easy to carry from one place to another.



2.The storage of the ladder

7 . Daily attention

1.The ladder's load is 330lb.Don't overload.
2.Do not use hard things to collide with ladders,that will cause them to be de-formed and unusable.
3.Keep the ladder safe.
4.Suggested indoor preservation.
5.If you can read the instructions well you won't hurt your hand.
6.Overseas products may be scratched or stained but it does not affect the use, please feel free to use it.

USER MANUAL

1.Important before using

Please read the instructions carefully and retain for future reference.

If you don't read the instructions properly and follow the instructions,you may get hurt during usage.

WARM REMINDER:Slight bending is normal when climbing ladders. Please don't worry.Ladders can hold up to 330lbs.





1.ENSURE that you are fit enough to use the ladder.Certain medical conditions,medication,alcohol or drug abuse could make ladder use unsafe.
2.When transporting ladders on roof bars or in a truck,ENSURE they are stably placed to prevent damage.
3.Inspect the ladder after delivery and before the first use to confirm condition and operation of all parts.
4.Visually check the ladder is not damage and safe to use at the beginning of each working day when the ladder is to be used.
5.For professional users,regular periodic inspection is required.
6.ENSURE the ladder is suitable for the task.
7.DO NOT use a damaged ladder.
8.Remove any contamination from the ladder,such as wet paint, mud, oil or snow.
9.Before using a ladder at work a rick assessment should be carried out respecting the legislation in the country of use.
10.DO NOT exceed 75 degree.
11.Ladder shall be on an even,level and unmovable base.
12.DANGER!Keep ladder away from power lines and live electronic circuits.
13.Ladder shall not be positioned on slippery surface(such as ice, shiny surface or significantly contaminated solid surface) unless additional effective measures are taken to prevent the ladder slipping or ensuring contaminated surfaces are sufficiently clean.
14.DO NOT overload ladder.Maximum weight of a person,tools and supplies is not to exceed the duty rating of 330 lbs(150kg).
15.DO NOT overreach.Users should keep their buckle(navel) inside the stiles and both feet on the same step/rung throughout the task.

2.Please read these 3 points below before use the ladder.


1.Tip: How to make sure the ladder is locked positively.

A From inner structure to understand





B from appearance to judge



2. The ladder is placed on the flat ground when it is used. The best inclination angle between the ladder and the ground is 75 degrees(as shown in the figure).



Tip!

It is suggested that two persons cooperate with each other and one person can hold the ladder below to ensure safety

3.For tall ladder,a balance bar at the bottom is a better option.

The way to install the balance bar:

1.Break the plastic rod of the slot with a hard object.
2.Insert the stabilizer bar into the slot.
3.You can choose to use the screws or not to use, both is OK.It's more stable if you screw it in.



1)fix two pcs orange plastic foot on stabiliser bar which close to wheels
2)fix two pcs black plastic foot on two side of stabiliser bar
3)break the plastic rod of the slot with a hard boject
4)insert the stabiliser bar into the slot,tight it by screw and bolt

3.The way to open the ladder

FULL EXTENSION OF THE LADDER

1.Place ladder on a firm and level ground,move one feet on the lowest rung(Scheme 1) .
2.To extend the ladder to its full height,start by pulling up the top rung until it locks into place.Pull up the next lower rung and continue until the ladder is fully opened(Scheme 2).
3.Check and make sure all latches are in the LOCKED position.



(Scheme 1)



(Scheme 2)

CAUTION Always check that all buttons are on the exact position "locked" ,before you climb on the ladder.

PARTIAL EXTENSION OF THE LADDER

1. Place ladder on a firm and level ground,move one feet on the lowest rung.
2.To extend the ladder to a partial height,by estimating the height you want, pull out one rungs of the ladder from the middle(scheme3) (each rung is 30/40cm apart) and then extend the other bottom rungs in turn(scheme 4) so that the first step is not too high and you can easily climb up
3.Check and make sure all latches are in the LOCKED position.




(scheme3)



(scheme 4)

4. The way to fold the ladder

For most people, it is a little difficult to fold the ladder rather than open it. However, it would be easier if you follow the steps below and no hurt to your hands:



1. Ladder on a firm and level ground make that the lowest rung begin.
2. Use one hand to grasp the ladder by a stile higher than the rung you are about to retract. Start with 2rd rung from the bottom.Use the other hand to push its latches,one after another, towards the centre of the rung and the next higher rung will drop down.
3. When the rungs of the ladder fall, do not let go of the ladder; after the rungs fall, retract the next level.
4. Secure the ladder with the closure starp