

MILESYN SXR HD 5W40 CJ-4

HEAVY DUTY FULL SYNTHETIC MOTOR OIL

MILESYN SXR HD 5W40 CJ-4 oil is a full synthetic, high performance, heavy-duty diesel engine oil that helps extend engine life while providing long drain capability and increased fuel economy for engines operating in severe conditions. MILESYN SXR HD 5W40 CJ-4 oil delivers exceptional performance in low emission engines including those with Exhaust Gas Recirculation (EGR), Diesel Particulate Filters (DPF's) and Diesel Oxidation Catalysts (DOC's).

Features and Benefits

- Excellent oxidation protection
- Superior low temperature flow properties
- Increased shear stability
- Enhanced fuel economy
- Protects against viscosity break down
- Improves engine cleanliness and reduces oil consumption
- Excellent cold engine starting in sub-zero temperatures
- Exceptional soot dispersancy
- Excellent wear control promotes optimal service life
- Minimizes maintenance downtime

Recommended for Applications

- API CJ-4/SN
- Mack EO-O Premium Plus
- Cummins CES 20081
- Detroit Diesel DDC 93K218
- CAT ECF-1a, ECF-2, ECF-3
- Volvo VDS-4
- Renault RLD-3

Applications

MILESYN SXR HD 5W40 CJ-4 oil is recommended for use in a wide range of heavy-duty applications and operating environments such as on-road transport, off-road construction and mining as well as agricultural applications.

Typical Properties

SAE Grade	5W40
Specific Gravity	.0850
Viscosity, cSt @ 100°C	14.40
Viscosity, CCS cP @ -30°C	6400
Viscosity, cSt @ 40°C	93.25
Viscosity Index	168
Pour Point, °C	-40
Zinc, Wt. (%)	0.134
Phosphorous, Wt. (%)	0.118
High Temp. / High Shear (HTHS)	4.1
TBN	9.2
NOACK, Wt. (%)	8.6