Manta | E24716-144BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

An undulating shape softly curls along its center to create an organic form constructed of a single panel of transparent acrylic. Further enhancing the form is the captivating effect of the frosted band around the borders and the patterned etching on the acrylic that captures the light. A coordinating wall sconce that features the same curled acrylic material and extends only 4 inches from the wall for ADA compliant applications.



*max overall height

MEASUREMENTS

DIMENSION	: 59" L x 9.75" W x 8.5" H
MAX OAH	: 120" OAH
CANOPY	: 4.754" W x 1.5" H x 23.5" L
HANGING WEIGHT	: 8 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 4,480 Rated (2,770 Del.)
BULB	: 1 x 56W LED DC Integrated , 56W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)
Gold (GLD)
Polished Chrome (PC)

GLASS

Clear Ribbed 144

MATERIAL

Aluminum,Steel,Acrylic

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com