

HOM115PCAFIC

Mini circuit breaker, Homeline, 15A, 1 pole, 120VAC, 10kA AIR, combo arc fault, plug on neutral, plug in, UL



Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	15 A
Certifications	UL Listed
Voltage Rating	120 V AC
Mounting Type	Plug-in
Number of Poles	1P
Short Circuit Current Rating	10 kA
Number of Spaces	1
Circuit Breaker Type	Combination ARC-fault
Ratings	HACR rated
Electrical Connection	Screw clamp terminals
Wire Size	AWG 14...AWG 8 aluminium/copper)1
Type of Packing	Clam packaging

Complementary

Connections - Terminals	Plug-on neutral
Tightening torque	35.40 lbf.in (4.0 N.m) 0.00...0.01 in ² (2.5...6 mm ²) (AWG 14...AWG 8)
Height	3.13 in (79.50 mm)
Width	1 in (25.40 mm)
Depth	2.98 in (75.69 mm)
Net Weight	0.66 lb(US) (0.30 kg)

Environment

Ambient Air Temperature for Operation	104 °F (40 °C)
---------------------------------------	----------------

Ordering and shipping details

Category	01321-HOMELINE 1 POLE BULK BRK
Discount Schedule	CPH
GTIN	785901978787
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.30 in (3.302 cm)
Package 1 Width	4.50 in (11.43 cm)
Package 1 Length	8.00 in (20.32 cm)
Package 1 Weight	9.60 oz (272.155 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	3
Package 2 Height	3.80 in (9.652 cm)

Package 2 Width	4.90 in (12.446 cm)
Package 2 Length	8.50 in (21.59 cm)
Package 2 Weight	33.60 oz (952.543 g)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Halogen content performance	Halogen free product

Contractual warranty

Warranty	Lifetime
----------	----------