



Gun cabinet disassembly instructions






PARTS LIST





INSTRUCTIONS

STEP 1




N*10

Link Ⓐ,Ⓒ,Ⓓ with Self tapping threads.

Note:The bottom screws are not installed.


STEP 2



Sides and back, use screw links

N*10

STEP 3




Bottom and cabinet, use screws to link




N*6

STEP 4




Top and cabinet, use screws to link

STEP 5


S*4
G
Lift the divider when it's in place,
put pressure on the divider

STEP 6


0*2
F
The back of the gun stock holder. The bayonet on both sides is bent at 90 degrees
H
F
N*4

OPENING YOUR SAFE FOR THE FIRST TIME

Touch the keypad area, enter the password 1234/123456, and press the "#" key to confirm. The speaker sounds "BI" long sound, then you can open the safe box

(Factory password is 123456# / 1234#)

PERSONAL PASSWORD SETTING

1. Press the setup button in the safe box .

2. When you hear a short “Di~,” the numeric keypad lights up. Enter a 1-8 digit password.. Press the “#” key.

3. The speaker sounds "B-" and the indicator blinks. At this time, enter the password again and press the "#" key. The speaker sounds "BI--" for a long time, indicating that the password is successfully set.

ADMINISTRATOR PASSWORD SETTINGS

1. After touch wake up, press “0,0” then press the setting button.

2. When you hear a short “Di~,” the numeric keypad lights up. Enter a 1-8 digit password.. Press the “#” key.

3. The speaker sounds "B-" and the indicator blinks. At this time, enter the password again and press the "#" key. The speaker sounds "BI--" for a long time, indicating that the password is successfully set.

THREE WAYS TO OPEN THE SAFE

1 . Emergency key + knob: For the first time, forget the password, and the battery is out of power. Insert the emergency key vertically, turn it to the left, and at the same time turn the knob to the right to open.

2. password + knob: Daily unlock. Enter the personal password or management password, press "#" or "", and then turn the knob to the right to open.

3. password + knob + External power Box: The internal battery is dead, the key is damaged or lost. Insert the external power box, enter the personal password or management password, press "#" or "*" , and then turn the knob to the right to open.

VIBRATION ALARM

1. Touch the keypad area, and press the “*” key. All lights will turn on, and you will hear a long “Di~,” indicating that the alert is activated. When the safe is shaken by external forces, the horn will issue an alarm for 1 minute. Enter the correct password to deactivate the alarm.

2. If the password is incorrectly entered, the speaker sounds "BIBIB". If the password is incorrectly entered for five consecutive times, the system locks for one minute.

RESTORE FACTORY SETTINGS

1. Long press the button for about 3 seconds (do not release), and the speaker

will sound "BI--" long

2. The user password is set to 1234. The management password is set to 123456.

MUTE FUNCTION

1. Press the number 1 key for 3 seconds, and the "RIGHT" indicator will be on for a long time, and the buzzer will be off.
2. Press the number 1 key for 3 seconds, and the "RIGHT" indicator will be on for a long time, and the buzzer will sound for a long time, and the buzzer will be on.

LOW VOLTAGE

When the voltage is equal to or less than 4.8V (+/-0.3V), you will hear a “Di Di Di, Di Di Di, Di Di Di” sound after entering the correct password or fingerprint to open the door, indicating that the battery is low and needs to be replaced to ensure normal use.