Project / Job Name:

Location:

Fixture Type:

Notes:



TH602 - 10 Watt; LED Commercial Track Head; Black; Cylinder; 24 Degree Beam Angle; H-Style

90+ CRI | DIMMABLE | ETL CLASSIFIED Intertek | FC | RoHS COMPLIANT | 50,000 HOURS | 120 VOLT | TITLE 24

GENERAL

Company	NUVO
EA Height	7.87
EA Width	2.56
EA Length	2.76
Bulb Included	Integrated
Extends (in)	7.38
Material	Die-cast Aluminum
Fixture Type	Track Head
Status	Active
Style	Contemporary
Surge Protection	Built-in surge protection - 1KV
Track Head Style	Cylinder
CCT Selectable	No
Wattage Selectable	No
Finish Family	Black
Amps	0.083A
Has Camera	No
IOT Enabled	No
Lens Material	Polycarbonate (PC)
Power Factor	0.92
SDS Class	LED_Fixture
Sloped Ceiling Compatible	Yes
Indoor Outdoor	Indoor
Product Technology	LED
Incandescent Equivalent	60W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	3000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	24
Color Temp	Warm White
CRI	90+
Dimming Type	120V only, Phase Cut (TRIAC)
Operating Frequency	60Hz
Operating Temp	-4F to +104F (-20C to +40C)
Lumens	600L
Volts	120v
Watts	10W

PHYSICAL

Lamp Base	Integrated
Finish	BLACK
ANSI Base	Integrated
Lamp Type	Integrated LED
Mounting Procedure	Track

ADDITIONAL INFO

Warranty	5-Years

PACKAGING

UPC	045923405129
Case Cube	0.5212
Case Height	8.66
Case Length	12.01
Case Quantity	12
Case UPC	10045923405126
Case Weight	9.18
Case Width	8.66
EA Cube	0.0322
EA Height	7.87
EA Length	2.76
EA Quantity	1
EA Weight	0.64
EA Width	2.56
Pack Type	Box
Web Height	2.0
Web Length	5.0
Web Width	2.0

COMPLIANCE

CA Prop 65	Lead
FCC Compliant	Yes
Location Rating	Dry
ROHS Compliant	Yes
Safety Listing	cETLus
California Ban	California T24 Listed
DLC Approved	No
Title 20	Exempt
T24/JA8 Compliant	Yes

© Satco Products, Inc.
All rights reserved 2026