



jalas® 3318

ASTM F2413-18 M/I/C/SD 35/PR ASTM F3445-21 SR EN ISO 20345:2022 S7, HRO

Learn more

A waterproof mid-cut safety boot with highest protection designed for comfort in cold environments. The grain leather and the durable textile upper protects feet and keeps them warm and features safety reflection strips. The oil and heat-resistant nitrile outer sole gives excellent grip and JALAS® aluminium toe cap, steel puncture protection and double impact protection zones in PORON® XRD® help keep feet safe in demanding conditions.

CHARACTERISTICS

- Highest level of protection
- Excellent grip
- Perfect fit
- Extra comfortable
- Excellent shock absorption

FUNCTIONS

- Waterproof Drylock-membrane
- ProNose toe reinforcement
- Heat-resistant outsole
- Oil-resistant outsole
- Anti-static properties
- Bellows tongue
- Padded boot shaft
- Ventilating insole
- Quick-tie
- Waterproof
- Reflector
- Double shock absorption zones
- Conforms with IEC 61340-5-1 (ESD)

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Toe injuries, Nail penetration, Antistatic, Wet feet

PRIMARY ENVIRONMENTS OF USE

Outdoors, All-year use, Environments with risk for outsole penetration, Wet environments, Harsh environments

SPECIFICATION

TYPE Safety footwear, Boots/Ankle boots
CATEGORY Cat. II
NAIL PROTECTION MATERIAL Steel
FITTING Regular
UPPER MATERIAL Full-grain leather, Textile
PRONOSE MATERIAL PU
TOECAP MATERIAL Aluminium
LINING MATERIAL Polyester, polyamide, Drylock membrane
INSOLE JALAS 8217 FX2 Climate
INNERSOLE MATERIAL Textile, Soft EVA, Polyester-based conductive thread, Merino wool, Double shock absorption zones in PORON® XRD®
MIDSOLE MATERIAL PU midsole
OUTSOLE MATERIAL Nitrile rubber outsole
FASTENING Laces
SHOELACES LENGTH 130 cm
COLOUR Black
NET WEIGHT, (SIZE 42) 1.48 kg

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

ASTM F2413-18
M/I/C/SD 35/PR

ASTM F3445-21
SR

EN ISO 20345:2022
S7, HRO

FEATURES

- Anti-static properties
- Ergothan Shock Absorption System
- ESD
- Aluminium toecap
- Oil-resistant outsole
- ProNose toe reinforcement
- Nail protection in steel
- Heat-resistant outsole
- Waterproof

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
36	3	4	5	3318-36	6408487427947
37	4	5	6	3318-37	6408487427954
38	5	5.5	6.5	3318-38	6408487427961
39	6	6.5	7.5	3318-39	6408487427978
40	6.5	7.5	8.5	3318-40	6408487427985
41	7	8	9	3318-41	6408487427992
42	8	9	10	3318-42	6408487428005
43	9	9.5	11	3318-43	6408487428012
44	10	10.5	11.5	3318-44	6408487428029
45	10.5	11	12.5	3318-45	6408487428036
46	11	12	13	3318-46	6408487428043
47	12	13	14	3318-47	6408487428050

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.