Fosso | E30334-BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Fosso delivers modern minimalism through a bold rectilinear body defined by a sharply angled backlit slit. Designed for outdoor use, the collection comes in 24", 35", and 47" lengths and features a 5CCT selectable switch for on-site color tuning. Finished in Matte Black and fully ADA compliant, Fosso combines a slim profile with a robust 120-277V commercial-grade LED driver, ideal for residential exteriors and demanding commercial faÃ§ades.



MEASUREMENTS

DIMENSION	: 5" W x 47.25" H x 1.5" Ext
BACK PLATE	: 5" W x 47.5" H
HANGING WEIGHT	: 1.1 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 4,000 Rated (1,400 Del.)
BULB	: 1 x 40W LED PCB Integrated , 40W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: TriacÂ orÂ ELVÂ atÂ 120V
CRI	: 90 CRI
COLOR_TEMP	: 22-27-30-35-40K

FINISHES OPTION

Black (BK)

MATERIAL

Aluminum, Glass

RATINGS

cETLus
Wet Location

ADDITIONAL

RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com