



SATCO LED lamps offer one of today's largest selections of LED products — providing solutions for the commercial, industrial and residential markets.

We bring quality, value and design to every product we create. With advancing technology, we improve performance, energy savings, safety, ease of installation and maintenance, and overall satisfaction.

We are your partners in success — from convenient packaging options and retail support to inventory supply.

SATCO is the lighting solution you can count on for the products you can rely on!



LED/CFL type A direct replacement lamps 4-pin (electronic ballasts)

- UL listed 4-pin 42 Watt direct replacement
- 4-pin lamps fit GX24q-4 sockets
- No re-wiring needed
- Instant on to full brightness / no flickering
- Vertical and horizontal options
- DLC Listed
- c-UL-us listed
- Up to 60% energy saving
- Long life—50,000 hours
- 5 Year warranty

Rotates 270°
when installed



S21400, S21401, S21402, S21403



S21404, S21405, S21406, S21407

LED/CFL Replacement Lamps - Ballast Compatible*



Item Number	Lamp Description	W	Base Type	CCT	CRI	M.O.L. (Inches)	Lm	Life/ Hrs.	UPC	Pack/ Mstr.
S21400	PLT/16W/H/LED/830/4P/DR	16	G24Q	3000K	82	6 3/8	1750	50K	045923224003	20
S21401	PLT/16W/H/LED/835/4P/DR	16	G24Q	3500K	82	6 3/8	1750	50K	045923224010	20
S21402	PLT/16W/H/LED/840/4P/DR	16	G24Q	4000K	82	6 3/8	1850	50K	045923224027	20
S21403	PLT/16W/H/LED/850/4P/DR	16	G24Q	5000K	82	6 3/8	1850	50K	045923224034	20
S21404	PLT/16W/V/LED/830/4P/DR	16	G24Q	3000K	82	5 3/4	1750	50K	045923224041	20
S21405	PLT/16W/V/LED/835/4P/DR	16	G24Q	3500K	82	5 3/4	1750	50K	045923224058	20
S21406	PLT/16W/V/LED/840/4P/DR	16	G24Q	4000K	82	5 3/4	1850	50K	045923224065	20
S21407	PLT/16W/V/LED/850/4P/DR	16	G24Q	5000K	82	5 3/4	1850	50K	045923224072	20

*Visit www.satco.com for ballast compatibility list.

Product sheet SA2471

See warranty for details.