





P/N	Internal P/N	CODES	LENGTH (xx)
DBC-26HDFW-05	K-DB26HDFBKC408	KDB408	1525 ⁺³⁰ ₋₁₀ mm
DBC-26HDFW-10	K-DB26HDFBKC410	KDB410	3050 ⁺³⁰ ₋₁₀ mm



PINOUT:

P1	COLOR	LABEL	P1	COLOR	LABEL
1	BLACK	P1	14	BROWN/BLACK	P14
2	BROWN	P2	15	RED/BLACK	P15
3	RED	P3	16	ORANGE/BLACK	P16
4	ORANGE	P4	17	YELLOW/BLACK	P17
5	YELLOW	P5	18	GREEN/BLACK	P18
6	GREEN	P6	19	BLUE/BLACK	P19
7	BLUE	P7	20	PURPLE/BLACK	P20
8	PURPLE	P8	21	GRAY/BLACK	P21
9	GRAY	P9	22	WHITE/BLACK	P22
10	WHITE	P10	23	PINK/BLACK	P23
11	PINK	P11	24	LIGHT GREEN/BLACK	P24
12	LIGHT GREEN	P12	25	LIGHT BLUE/BLACK	P25
13	LIGHT BLUE	P13	26	BROWN/WHITE	P26
			SHELL	DRAIN	

PVC Individual bag:

- Label#:DB26 female to lead wire,5ft DBC-26HDFW-05 Rev A1
DB26 female to lead wire,10ft DBC-26HDFW-10 Rev A1
- Label#:Prop65 label or print
- Bare End wires require wrapping protection Bundle PVC bag
Per 10 pcs individuals packed together
Label#: DBC-26HDFW-05 10pcs YYWW(date code)
Label#: DBC-26HDFW-10 10pcs YYWW(date code)

SPEC:

- CABLE:UL2464 28AWG*26C+DRAIN+AL JACKET BLACK IN COLOR OD:6.5mm.
- DB 26P FEMALE TYPE BLACK COLOR SHELL NICKEL PLATED.
- HEAT SHRINK TUBE LABEL WHITE IN COLOR L=15mm.
- MOLDING SCREW 4-40UNC 4*38.5mm.
- MOLDING PVC(UL94-V0) BLACK IN COLOR.
- DUST CAP.

REV	DATE	PROJECTION	DRAWN BY	CHECKED BY	SALES	APPROVAL BY
A/0	2025-12-22	milan	2025-12-22			
			SCALE:	UNIT:mm	DATE:2025-12-22	

CompuCable^{USA}

Model Name:

D-Sub High Density DB26 Female
RS-232 Serial Cable to Lead Wires

Codes

SHEET NO.

P/N:

DBC-26HDFW-**