Joist | E24930-DWCHL

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Horizontal Spans of natural wood frame an evenly diffused LED omnidirectional light source. Choose from genuine Walnut with Black or Natural Aged Brass accents or solid oak in a hand-applied Driftwood finish. Whether surface mounted or suspended as a pendant, this collection provides a natural touch to an otherwise modern, minimalist design.



MEASUREMENTS

DIMENSION	: 21.75" W x 4.75" H x 4.75" Ext
CANOPY	: 4.75" W x 1.5" H x 4.75" L
HANGING WEIGHT	: 2.7 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 1,040 Rated (780 Del.)
BULB	: 1 x 13W LED DC Integrated , 13W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

- Antique Brass (AB)
- Driftwood / Charcoal (DWCHL)
- Walnut / Black (WNBK)

MATERIAL

Wood, Acrylic, Aluminum, Steel

RATINGS

cETLus
Damp Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com