



P65

Technical Data



Bouton® Optical Zenon Z11sm™ Foam

Rimless Safety Glasses with Black Temple, Gray Lens, Foam Padding and Anti-Scratch / Anti-Fog Coating

- Ideal for women and men with narrow faces
- Foam padding design forms a seal to keep out dust and airborne particles
- Lightweight, rimless design provides all day user comfort
- Thin, flexible temples provide a secure fit without uncomfortable pressure points
- Molded nose bridge design to fit the vast majority of users
- 11 Base curve lens
- Meets ANSI Z87.1+
- ⚠ **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Dusty Work Areas
- Outdoor Work
- Construction Applications
- Public Works

Color	Black
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	25.59 x 10.24 x 12.60
Case Weight (lbs)	13.23
Country of Origin	Taiwan
Lens	Tinted
Frame Style	Foam-Lined
Lens Color	Gray
Frame Fit	Narrow Face
Lens Coating	Anti-Fog
Bridge	Molded
Temple	Molded
Base Curve	11
Construction	Womans Fit
Certifications	ANSI Z87.1, TAA Compliant
Product Circularity	Recycled via Terracycle

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-13

SKU Information

SKU	FRAME COLOR	LENS	LENS		UPC	UPC (INNER)	UPC (CASE)
			LENS COLOR	COATING			
250-00-0000	Black	Clear	Clear	AS	616314059230	01616314059239	02616314059238
250-00-0001	Black	Tinted	Gray	AS	616314059247	01616314059246	02616314059245
250-00-0002	Black	I/O	Clear	AS	616314059254	01616314059253	02616314059252
250-00-0020	Clear	Clear	Clear	AS/AF	616314117244	01616314117243	02616314117242
250-00-0900	Clear	Clear	Clear	AS	616314059261	01616314059260	02616314059269
250-00-0920	Black	Clear	Clear	AS/AF	616314059278	01616314059277	02616314059276
250-00-F020	Black	Clear	Clear	AF	616314380143	10616314380140	20616314380147
250-00-F021	Black	Tinted	Gray	AF	616314375231	10616314375238	20616314375235
250-00-F051	Black	Tinted	Light Gray	AF	616314375279	10616314375276	20616314375273

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated