

## Special Tec F ECO SAE 5W-20

### Description

Fully synthetic motor oil specifically designed for certain Ford Eco Boost engines. A unique additive package provides a engine clean, offers superior lubrication and supports higher fuel economy. Recommended when a Ford WSS-M2C 925-B specification is required.

### Properties

- outstanding engine cleanliness
- outstanding lubrication reliability
- instant lubrication after cold start
- high resistance to aging
- ideal with catalytic converters
- stable to oxidation

### Specifications / Approvals

ACEA C5 • API SN • Ford WSS-M2C 948-B

**LIQUI MOLY recommends this product for vehicles or assemblies for which the following specifications or original spare part numbers are required:**

Jaguar / Land Rover STJLR.03.5004

### Technical data

|                           |                                       |
|---------------------------|---------------------------------------|
| SAE class (engine oils)   | 5W-20<br>SAE J 300                    |
| Density at 59 °F          | 0,850 g/cm <sup>3</sup><br>DIN 51757  |
| Viscosity at 104 °F       | 46,0 mm <sup>2</sup> /s<br>ASTM D7042 |
| Viscosity at 212°F        | 8,3 mm <sup>2</sup> /s<br>ASTM D7042  |
| Viscosity at -31 °F (MRV) | < 60000 mPas<br>ASTM D4684            |
| Viscosity at -22 °F (CCS) | ≤ 6600 mPas<br>ASTM D5293             |
| Viscosity index           | 160<br>DIN ISO 2909                   |
| HTHS at 302 °F            | ≥ 2,6 mPas<br>ASTM D5481              |
| Pour point                | -38 °F<br>DIN ISO 3016                |
| Flash point               | 428 °F<br>DIN ISO 2592                |
| Evaporation loss (Noack)  | 11,0 %<br>CEC-L-40-A-93               |
| Total base number         | 8,5 mg KOH/g<br>DIN ISO 3771          |



### Technical data

|                     |                           |
|---------------------|---------------------------|
| Sulfate ash         | ≤ 0,8 g/100g<br>DIN 51575 |
| Color number (ASTM) | L 3,5<br>DIN ISO 2049     |

### Areas of application

For gasoline engines where a motor oil according to current specifications is required or recommended. Tested safe with catalytic converters and turbochargers.

**⚠ WARNING:** This product can expose you to chemicals including toluene, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

### Application

Observe the manufacturers instructions!

### Available pack sizes

|                          |                         |
|--------------------------|-------------------------|
| 1 l Canister plastic     | 2263<br>CAEN-CAFR-USEN  |
| 5 l Canister plastic     | 2264<br>CAEN-CAFR-USEN  |
| 20 l Canister plastic    | 20126<br>CAEN-CAFR-USEN |
| 205 l Black plate barrel | 22115<br>CAEN-CAFR-USEN |

**Our information is based on thorough research and may be considered reliable, although not legally binding.**