

Alumilux Outline | E41329-BK


Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____







PRODUCT DESCRIPTION



MEASUREMENTS

DIMENSION	: 4.5" W x 4.5" H x 0.75" Ext
BACK PLATE	: 4.25" W x 4.25" H x 3.25" HCO
HANGING WEIGHT	: 0.72 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 560 Rated (70 Del.)
BULB	: 1 x 8W LED PCB Integrated , 8W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: ELV
CRI	: 90+ CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Omni

FINISHES OPTION

- Black (BK)
- Satin Aluminum (SA)
- White (WT)

MATERIAL

Aluminum, Acrylic

RATINGS

cETLus
Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Any
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

PHOTOMETIC: Report Found Online

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com