Steppes | E41552-ANB

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

A slim profile extends from the wall with sharply angled facets. Available in various sizes and your choice of Matte Black or Antique Bronze finish, its scale allows it to function both as a step light and as a subtle LED outdoor wall sconce. Concealed within the top housing is an integrated LED light that casts light downward on a series of ridges capturing various intensities of light.



MEASUREMENTS

DIMENSION	: 4.75" W x 4.75" H x 1" Ext
BACK PLATE	: 4.75" W x 4.75" H x 2.25" HCO
HANGING WEIGHT	: 0.88 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 1,000 Rated (450 Del.)
BULB	: 1 x 10W LED AC Integrated , 10W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Down

FINISHES OPTION

Antique Bronze (ANB)
Black (BK)

MATERIAL

Aluminum

RATINGS

cETLus
Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Down
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com