
Elysian | E11083-124NAB

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Segments of Clear glass cylinders are separated by distinctly rippled Clear crystal fonts on a thin Natural Aged Brass frame. The translucent segments are backlit with integrated LED illumination creating an airy, ethereal composition of glass textures. Available in vertical and horizontal configurations as well as sconce and portable configurations.



MEASUREMENTS

DIMENSION	: 41.5" L x 5.5" W x 5.5" H
MAX OAH	: 120" OAH
CANOPY	: 4.75" W x 1.75" H x 4.75" L
HANGING WEIGHT	: 16.5 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 2,300 Rated (1,610 Del.)
BULB	: 3 x 28W LED DC Integrated , 28W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Natural Aged Brass (NAB)

GLASS

Ripple 124

MATERIAL

Steel, Aluminum, Glass

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com