



Project / Job Name:

Location:

Fixture Type:

Notes:

65-942 - 45/60/80 Watt; 3K/4K/5K CCT Selectable LED Semi Cutoff Wall Pack; 120-277 Volt; Bronze Finish



GENERAL

Company	NUVO
EA Height	6.3
EA Width	7.28
EA Length	13.39
Bulb Included	Integrated
Dimmable Text	0-10V Dimming
Extends (in)	5.26
Material	Die-cast Aluminum
Fixture Type	Wall Pack
Status	Active
Style	Utility
Surge Protection	Built-in surge protection - 4KV
Total Harmonic Distortion	11.60%
CCT Selectable	Yes
Wattage Selectable	Yes
Finish Family	Bronze
Amps	0.375-0.162/0.500-0.217/0.667-0.289A
Integrated Features	Integrated Photocell
IOT Enabled	No
Lens Finish	Opaque
Lens Material	Impact Resistant PC
Lensed	Yes
Photo Cell	Yes - Bypassable
Power Factor	>0.9
Indoor Outdoor	Outdoor
Product Technology	LED

ELECTRICAL

CCT (Kelvin Temp)	3000K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	55x105
Color Temp	Soft White to Natural Light
CRI	80+
Dimming Type	0-10V Dimming
Operating Frequency	50/60Hz
Operating Temp	-40C (-40F) to +40C (+104F)
HID Equivalent	100W-250W
Lumens	7243L-12436L
Volts	120V-277V
Watts	45W/60W/80W

PHYSICAL

Lamp Base	Integrated
Finish	BRONZE
ANSI Base	Integrated
Lamp Type	Integrated LED

ADDITIONAL INFO

Warranty	5-Years
----------	---------

PACKAGING

UPC	045923410284
Case Cube	1.7826
Case Height	13.98
Case Length	15.55
Case Quantity	4
Case UPC	10045923410281
Case Weight	22.71
Case Width	14.17
EA Cube	0.3554
EA Height	6.3
EA Length	13.39
EA Quantity	1
EA Weight	4.94
EA Width	7.28
Pack Type	Box
Web Height	5.83
Web Width	12.62

COMPLIANCE

Bug Rating	B1-U4-G3
CA Prop 65	Lead
DLC ID	S-VC4ZR0
FCC Compliant	Yes
IP Rating	IP65
Location Rating	Wet
ROHS Compliant	Yes
Safety Listing	cULus - Certified
California Ban	Lawful for sale
DLC Approved	Yes
Title 20	Exempt
T24 Compliant	No