Project / Job Name:

Location:

Fixture Type:

Notes:



65-1673 - 20/30/40 Wattage Selectable LED 1ft x 4ft Backlit Panel; 35K/4K/5K CCT Selectable; 120-347 Range Voltage; White Finish

GENERAL

Company	NUVO
EA Height	12.52
EA Width	2.91
EA Length	48.46
Bulb Included	Integrated
Material	Die-cast Aluminum
Fixture Type	Flat Panel
Status	Active
Style	Utility
Surge Protection	Built-in surge protection - 2KV
Total Harmonic Distortion	<20%
CCT Selectable	Yes
Wattage Selectable	Yes
Finish Family	White
Amps	0.050-0.340A
Has Camera	No
IOT Enabled	No
Lens Finish	White
Lens Material	Polystyrene (PS)
Lensed	Yes
Power Factor	0.9
Indoor Outdoor	Indoor
Product Technology	LED
Incandescent Equivalent	200W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	3500K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	120
Color Temp	Neutral White to Natural Light
CRI	80+
Dimming Type	0-10V Dimming
Operating Frequency	50/60Hz
Operating Temp	+1.4F to +113F (-17C to +45C)
Lumens	2500L/3750L/5000L
Volts	120V-347V
Watts	20W/30W/40W
Max Lumens	5000L
Connection	Hardwire

PHYSICAL

Lamp Base	Integrated
Finish	WHITE
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Rectangle
Mounting Procedure	Ceiling

ADDITIONAL INFO

Warranty	5-Years

PACKAGING

UPC	045923411854
Case Cube	1.0217
Case Height	12.52
Case Length	48.46
Case Quantity	2
Case UPC	10045923411851
Case Weight	9.83
Case Width	2.91
EA Cube	1.0217
EA Height	12.52
EA Length	48.46
EA Quantity	1
EA Weight	9.83
EA Width	2.91
Pack Type	Box
Web Height	1.38
Web Length	47.76
Web Width	11.93

COMPLIANCE

CA Prop 65	Lead
DLC ID	S-ZT74D1; S-FLQ6J0
FCC Compliant	Yes
IP Rating	IP20
Location Rating	Damp
NSF Approved	Yes
ROHS Compliant	Yes
Safety Listing	cULus - Certified
California Ban	Lawful for sale
DLC Approved	Yes
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026