MASTER®
THE PROFESSIONAL'S CHOICE SINCE 1953

Master MAC-30POSC 30" High Velocity Pedestal Fan—7550 CFM, 1/4 HP, 120 Volt




- DURABLE—great for your home, garage, barn, or outside event
- POWERFUL—steel construction
- INDUSTRY-LEADING—high airflow for up to 7550 CFM
- Machined industrial motor, swivel head, adjustable height post, OSHA-compliant safety grille, and more
- 1-year limited warranty

Product Description

When you need to cool down quickly, look no further than Master's industry-leading, 30" High Velocity Pedestal Fan. The heat of summer is no match for its powerful, direct-drive motor and long-lasting steel construction. Plus, the swivel head and adjustable height post give you unrivaled versatility for all your cooling needs. Whether you're in the barn, relaxing at home, or working in the garage, this fan will do the job while giving your A/C and wallet a rest.

Master – built for power.



©2026 Pinnacle Climate Technologies

Features and Benefits

- Great for your home, garage, barn, or outside event
- Powerful steel construction
- High airflow for up to 7550 CFM
- 1/4 HP industrial motor
- Oscillating Fan Head for Maximum Airflow Control
- Rock-solid, OSHA-compliant safety grille
- 3 speed settings
- Adjustable height post
- Steel fan blades
- 1-year limited warranty

Key Specs

Model Number	MAC-30POSC
Brand	Master
Warranty	1-year limited warranty
Net Weight (lb.)	57
Air Flow (CFM)	7550 / 6800 / 5800
Motor Size (HP)	1/4
Variable Speed	Yes
Volts	120
Amps	1.7
Dimensions (L x W x H) (in.)	41 x 8 x 35

Master is a registered trademark of Pinnacle Climate Technologies, Inc.

©2026 Pinnacle Climate Technologies