



Technical Data

Color	Black
Sizes Available	7-11
Polymer	Butyl
Thickness	12 Mil
Lining	Unlined
Length	14"
Cuff	Rolled
Grip	Rough
Construction	Unsupported, ESD Safe
Case Dimensions (in)	22.83 x 14.96 x 7.48
Case Weight (lbs)	0.00
Packed	48 Pair/Case
Packaging	Bagged Pair
Certifications	TAA Compliant, EN 16350
Country of Origin	Germany

Assurance®

12 Mil Butyl Rubber Glove with Rough Grip-14"

- 12 Mil Bromine Butyl Rubber ideal for incidental splash and acute chemical exposure
- Bromine enhances temperature resistance, offering superior durability
- Designed to handle extreme exposure to exposure to polar organic compounds such as ketones, carboxylic acids, esters, and amine derivatives
- 14 " length for extended forearm protection
- Rough finish to maintain a better grip
- Tested to EN 16350 for electrostatic properties to help protect any static sensitive materials or equipment

Performance Data

EN 374	ABIKLNOT
EN 388	001X
EN 374-5	Bacteria, Fungi and Virus

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
BUT03R/7	Black	7	616314941603	10616314941600	20616314941607
BUT03R/8	Black	8	616314941689	10616314941686	20616314941683
BUT03R/9	Black	9	616314941726	10616314941723	20616314941720
BUT03R/10	Black	10	616314941801	10616314941808	20616314941805
BUT03R/11	Black	11	616314949500	10616314949507	20616314949504