



jalas® ZENIT 1718

ASTM F2413-18 M/I/C/SD 35/PR EN ISO 20345:2022 S3, SR, FO, SC, LG

Learn more

A soft, light and ergonomic mid-cut safety boot with BOA® Fit System and highest (S3) level protection. The PU-coated and split leather upper offer water repellent properties and great fit for long days on your feet. An oil-resistant RPU outer sole gives enhanced grip and the ventilated inner sole keeps feet cool. Features our JALAS® aluminium toe cap, steel puncture protection and double impact protection zones in PORON® XRD®.

CHARACTERISTICS

- Highest level of protection
- Excellent grip
- Perfect fit
- Extra comfortable
- Excellent shock absorption

FUNCTIONS

- ProNose toe reinforcement
- Oil-resistant outsole
- Anti-static properties
- Bellows tongue
- Padded boot shaft
- Ventilating insole
- Quick-tie
- Stabilizator
- Pull loops
- Water repellent
- Double shock absorption zones
- Conforms with IEC 61340-5-1 (ESD)

BOA DIALED IN. PRECISION FIT. Xrd PROTECTION LEATHER WORKING GROUP

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Toe injuries, Nail penetration, Antistatic

PRIMARY ENVIRONMENTS OF USE

Outdoors, All-year use, Environments with risk for outsole penetration

SPECIFICATION

TYPE Safety footwear, Boots/Ankle boots
CATEGORY Cat. II
NAIL PROTECTION MATERIAL Steel
FITTING Regular
COLLECTION Zenit
UPPER MATERIAL PU-coated leather, Split leather
PRONOSE MATERIAL PU
TOECAP MATERIAL Aluminium
LINING MATERIAL Polyester, polyamide
INSOLE JALAS 8217 FX2 Climate
INNERSOLE MATERIAL Textile, Soft EVA, Polyester-based conductive thread, Merino wool, Double shock absorption zones in PORON® XRD®
MIDSOLE MATERIAL PU midsole
OUTSOLE MATERIAL RPU outsole
FASTENING BOA® Fit System
COLOUR Black
NET WEIGHT, (SIZE 42) 1.39 kg

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

ASTM F2413-18
M/I/C/SD 35/PR

EN ISO 20345:2022
S3, SR, FO, SC, LG

FEATURES

- Anti-static properties
- Ergothan Shock Absorption System
- ESD
- Aluminium toecap
- Oil-resistant outsole
- ProNose toe reinforcement
- Nail protection in steel
- Stabilizator
- Water repellent

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
36	3	4	5	1718-36	6408487501678
37	4	5	6	1718-37	6408487501685
38	5	5.5	6.5	1718-38	6408487501692
39	6	6.5	7.5	1718-39	6408487501708
40	6.5	7.5	8.5	1718-40	6408487501715
41	7	8	9	1718-41	6408487501722
42	8	9	10	1718-42	6408487501739
43	9	9.5	11	1718-43	6408487501746
44	10	10.5	11.5	1718-44	6408487501753
45	10.5	11	12.5	1718-45	6408487501760
46	11	12	13	1718-46	6408487501777
47	12	13	14	1718-47	6408487501784

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.