



Technical Data

Color	Green
Sizes Available	S/M-2XL
Packaging	Bagged Each
Packed	10/Case
Case Weight (lbs)	0.00
Country of Origin	Mexico
Certifications	TAA Compliant
Harness Points of Adjustment	5
Harness Style	H
Extended D-Ring	No
Coated	No
Harness Integrated Padding	Yes
Harness Integrated Chair	No
Harness Reflective Webbing	No
Webbing Material	Polyester
Harness Lumbar Support	No

Miller® H500

Industry Standard Full-Body Harness with 5 Points of Adjustment, Back D-Ring, Mating Chest Buckles & Tongue Leg Buckles

- New specially formulated webbing flexes to accommodate movement and body contours for optimum comfort
- Detachable soft shoulder pads for added comfort
- Waist pad with adequate foam density for optimum lumbar support
- New ergonomically designed pressure-relief breathable shoulder/back padding keeps workers drier and cooler
- Smart anti-tangle design for a hassle-free donning experience
- Dedicated SRL web link for easy attachment of personal SRLs
- User-friendly resettable lanyard keepers allow users to attach lanyard when not in use
- Clearly identifiable smart impact indicators for hassle-free inspection
- Rated to 420 lb (max. weight capacity)
- Certified to OSHA 1926.502, ANSI Z359.11, and CSA Z259.10 standards
- This harness is ideal for industrial workers seeking safety, comfort, and ease of use during demanding tasks

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
H5ISP311001	Green	S/M	612230242169		
H5ISP311002	Green	L/XL	612230242176		
H5ISP311003	Green	2XL	612230242183		