Project / Job Name:

Location:

Fixture Type:

Notes:



S30100 - LED Mini Task Light; 600 Max Lumens; USB-C Rechargeable; 3.7 Volt; 15pc Tray Pack

GENERAL

Company	SATCO
EA Height	3.0
EA Width	3.75
EA Length	1.25
Material	Aluminum / ABS Plastic / Polycarbonate (PC)
Fixture Type	Rechargeable Task
Includes	USB-A to USB-C Charging Cable
Product Notes	Integrated Rechargeable 3.7V Li-ion Battery; Charge Time: 3HRS
Status	Active
CCT Selectable	Yes
Wattage Selectable	No
Finish Family	Black
Additional Info	Ships in retail-ready display trays and packaging
Integrated Features	CCT Selectable; Adjustable Magnetic Base; Tripod Mount; Turbo; Strobe; Red Light
Lens Finish	Clear
Lens Material	Polycarbonate (PC)
Lensed	Yes
Portable Light Modes	2700K, 3200K, 4500K, 5400K, High, Low, Medium, Strobe, Turbo
Product Technology	LED
Serviceable Battery	No
Beam Distance (Ft)	115
Battery Indicator	Yes
Digital Display	No
Drop Impact Rating	3.28 Ft (1M)
Battery Operating Temp	+32F to +104F (0C to +40C)
Light Source Quantity	Single
Power Bank Storage	1200mAh

ELECTRICAL

CCT (Kelvin Temp)	5400K/4500K/3200K/2700K
Dimmable	Yes-Dimmable
Color Temp	Warm White to Natural Light
CRI	50+
Dimming Type	Only dimmable via setting selection, Step Dimming
Operating Temp	+32F to +104F (0C to +40C)
Lumens	600L/500L/120L/40L
Volts	3.7V
Max Lumens	600L
Connection	USB-C Rechargeable
Charge Time	3hr
Battery Chemistry	LiFePO4
Replaceable Battery Type	103040
USB Type In	1 USB-C

PHYSICAL

Finish	Black / Gray / Red
Housing Color	BlackGrayRed
Mounting Procedure	Hang Hook, Magnetic Base, Stand Base, Tripod Mount

ADDITIONAL INFO

Warranty	1-Year
Installation Notes	Do Not Charge The Product Below 40F Or above 104F; Do Not Exceed 5V DC, 1A Charging
Portable Light Functions	CCT Selectable Function, Red Light Function, White Light Function

PACKAGING

UPC	045923300011
Case Cube	1.1742
Case Height	10.16
Case Length	12.68
Case Quantity	60
Case UPC	10045923300018
Case Weight	18.95
Case Width	15.75
EA Cube	0.0081
EA Height	3.0
EA Length	1.25
EA Quantity	1
EA Weight	0.22
EA Width	3.75
Inner Cube	0.2079
Inner Height	4.41
Inner Length	6.97
Inner Quantity	30
Inner UPC	20045923300015
Inner Weight	9.5
Inner Width	11.69
Pack Type	Color Box
Web Height	1.1
Web Length	2.2
Web Width	2.4

COMPLIANCE

CA Prop 65	Lead
FCC Compliant	Yes
IP Rating	IP44
ROHS Compliant	Yes
Energy Star Certified	No
T24/JA8 Compliant	No
Performance Standards	ANSI PLATO FL1

© Satco Products, Inc.
All rights reserved 2026