


PRODUCT DESCRIPTION

Elipses of Arches and Ovals are finishes in your choice of Black or Gold. The mirrors feature discreet LED channels along their frame. Whereas white acrylic diffusers pair with Gold frame, the Black mirrors are even less conspicuous featuring a black diffuser along the mirror edge appearing as if there is no light source when turned off.



MEASUREMENTS

DIMENSION	: 24" W x 36" H x 1.75" Ext
HANGING WEIGHT	: 16.94 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 5,200 Rated (1,700 Del.)
BULB	: 1 x 52W LED PCB Integrated , 52W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Dimmable on touch switch
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Indirect

FINISHES OPTION

Black (BK)
Gold (GLD)
Satin Nickel (SN)

MATERIAL

Aluminum, PC, Glass

RATINGS

cETLus
Damp Location
CA Title 24

ADDITIONAL

INSTALL UP/DOWN: Vertical / Hori
RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com