

TOULOUSE

504-42-VB

FINISHES

VINTAGE BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 29"

Width/Diameter: 42"

Minimum Height: 34"

Maximum Height: 102"

Canopy/Backplate: 18"

Hanging Type: 72" Chain

Product Weight: 88.0457lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: Yes

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: Light Bronze

Shade 1 Top Width: 13"

Shade 1 Height: 7.75"

Shade 2: Acrylic

Shade 2 Finish: Opal Glossy

Shade 2 Top Width: 2.25"

Shade 2 Height: 24.25"



ELECTRICAL



Bulb 1

Bulb Included: N/A

Socket: Integrated LED

Bulb Type: LED

Max Wattage: 44

Bulb Quantity: 6

Bulb Included: Yes

Wire Length: 144"

Cord Type: SPT-1 SILVER W/ TINNED GROUND
WIRE

Dimmer Type: TRIAC, 0-10 VOLT

Gem Box Required (2"x3"): No

Dark Sky: No

CRI: 90

Color Temp.: 2700k

Lumens: 1875

Title 24: No

Field Serviceable: Yes

SHIPPING

Carton 1: 44" x 30" x 38"

Carton 1 Weight: 121lb

Shipping Method: Truck Only

Country of Origin: VN

