

HUDSON VALLEY LIGHTING GROUP

Hudson Valley Lighting | Troy Lighting | Mitzi | Corbett Lighting



WARNING/CAUTION

- DISCONNECT POWER BEFORE RE-LAMPING OR WIRING THE FIXTURE. READ ALL INSTRUCTIONS COMPLETELY BEFORE STARTING INSTALLATION.
- TO AVOID THE RISK OF FIRE OR SHOCK, FIXTURE MUST BE INSTALLED IN COMPLIANCE WITH ALL APPLICABLE NATIONAL AND LOCAL ELECTRICAL/BUILDING CODES. THE INSTALLATION AND MAINTENANCE OF THIS UNIT SHOULD BE COMPLETED BY A LICENSED ELECTRICIAN OR CERTIFIED FACTORY TRAINED TECHNICIAN.
- CALIFORNIA PROP 65: THIS LIGHTING FIXTURE CONTAINS CHEMICALS KNOWN TO THE STATE OF CALIFORNIA TO CAUSE CANCER, BIRTH DEFECTS, AND/OR OTHER REPRODUCTIVE HARM. WASH HANDS AFTER USE.
- UNPACK FIXTURE, PARTS AND PARTS BAG(S) BEFORE DISCARDING THE CARTON. MAKE CERTAIN THAT ALL PARTS ARE FOUND. INSPECT THE FIXTURE PRIOR TO INSTALLATION FOR ANY DAMAGE. HVLG DOES NOT PAY OR REIMBURSE ELECTRICIAN FEES. FIXTURE MAY NOT BE RETURNED ONCE IT HAS BEEN INSTALLED. SEE WARRANTY FOR EXCEPTIONS.
- PLEASE CLEAN WITH A SOFT, DRY CLOTH ONLY! DO NOT USE CLEANSERS.



ATTENTION PRUDENCE

- DÉBRANCHEZ L'ALIMENTATION AVANT DE REMPLIR OU DE CÂBLER LE LUMINAIRE. LISEZ COMPLÈTEMENT TOUTES LES INSTRUCTIONS AVANT DE COMMENCER L'INSTALLATION
- POUR ÉVITER LE RISQUE D'INCENDIE OU D'ÉLECTROCUTION, LE LUMINAIRE DOIT ÊTRE INSTALLÉ CONFORMÉMENT À TOUS LES CODES ÉLECTRIQUES/DE CONSTRUCTION NATIONAUX ET LOCAUX APPLICABLES. L'INSTALLATION ET L'ENTRETIEN DE CET APPAREIL DOIVENT ÊTRE EFFECTUÉS PAR UN ÉLECTRICIEN AGRÉÉ OU UN TECHNICIEN CERTIFIÉ FORMÉ EN USINE.
- CALIFORNIE PROP 65 : CET APPAREIL D'ÉCLAIRAGE CONTIENT DES PRODUITS CHIMIQUES CONNUS PAR L'ÉTAT DE CALIFORNIE POUR PROVOQUER LE CANCER, DES MALADIES CONGÉNITALES ET/OU D'AUTRES DOMMAGES À LA REPRODUCTION. LAYER LES MAINS APRÈS UTILISATION.
- DÉBALLEZ LE LUMINAIRE, LES PIÈCES ET LE(S) SAC(S) DE PIÈCES. AVANT DE JETER LE CARTON. ASSUREZ-VOUS QUE TOUTES LES PIÈCES SONT TROUVÉES. INSPECTEZ LE LUMINAIRE AVANT DE L'INSTALLER POUR DÉTECTER TOUT DOMMAGE. HVLG NE PAIE NI NE REMBOURSE LES FRAIS D'ÉLECTRICITÉ. LE LUMINAIRE NE PEUT PAS ÊTRE RETOURNÉ UNE FOIS QU'IL A ÉTÉ INSTALLÉ. VOIR GARANTIE POUR LES EXCEPTIONS.
- VEUILLEZ NETTOYER UNIQUEMENT AVEC UN CHIFFON DOUX ET SEC ! N'UTILISEZ PAS DE NETTOYANTS.




PRECAUCIÓN ADVERTENCIA

- DESCONECTE LA CORRIENTE ANTES DE VOLVER A ENCENDER O CONECTAR EL APARATO. LEA TODAS LAS INSTRUCCIONES ANTES DE COMENZAR LA INSTALACIÓN.
- PARA EVITAR EL RIESGO DE INCENDIO O DESCARGA ELÉCTRICA, LA INSTALACIÓN DEBE SER REALIZADA DE CONFORMIDAD CON TODOS LOS CÓDIGOS DE CONSTRUCCIÓN / ELÉCTRICOS NACIONALES Y LOCALES APPLICABLES. LA INSTALACIÓN Y EL MANTENIMIENTO DE ESTA UNIDAD DEBE SER REALIZADO POR UN ELECTRICISTA LICENCIADO O UN TÉCNICO CAPACITADO POR UNA EN FÁBRICA CERTIFICADORA.
- CALIFORNIA PROP 65: ESTE APARATO DE ILUMINACIÓN CONTIENE PRODUCTOS QUÍMICOS QUE EL ESTADO DE CALIFORNIA SE CONOCE POR CAUSAR CÁNCER, DEFECTOS DE NACIMIENTO Y / U OTROS DAÑOS REPRODUCTIVOS. LAVARSE LAS MANOS DESPUÉS DEL USO.
- DESEMBALA LOS ACCESORIOS, REPUESTOS Y BOLSA (S) DE REPUESTOS. ANTES DE DESECHAR LA CAJA. ASEGÚRESE DE ENCONTRAR TODAS LAS PIEZAS. INSPECCIONE EL ACCESORIO ANTES DE LA INSTALACIÓN POR CUALQUIER DAÑO. HVLG NO PAGA NI REEMBOLSA LAS TARIFAS DEL ELECTRICISTA. EL ACCESORIO NO SE PUEDE DEVOLVER UNA VEZ QUE SE HAYA INSTALADO. CONSULTE LA GARANTÍA PARA EXCEPCIONES.
- ¡LIMPIE CON UN PAÑO SECO Y SUAVE ÚNICAMENTE! NO USE LIMPIADORES.

CORBETT


SERENITY 228-43 Installation Instructions



FIXTURE INSTALLATION

1. Feed the wire through the FIXTURE STEM (O), STEM (N) and twist tightly onto the FIXTURE ASSEMBLY (Q). Keep adding additional stems until your desired hanging height is met.
2. Thread the CONNECTOR (M) to the STEM (N). Slide in the CANOPY ACCENT (T), CANOPY (S) onto the STEM (N), then thread the SWIVEL (G) onto the CONNECTOR (M). Attach the SWIVEL BLOCK (D) above the CANOPY (S) and secure using HEX NUTS (C).
3. Pull the wire out from the junction box, and install the MOUNTING PLATE (A) onto the junction box using the MOUNTING SCREWS (B). This fixture is designed to be mounted on standard round or octagon junction box. The junction box must be securely mounted to the structure of the building. Thread the STUDS (I) unto the MOUNTING PLATE (A). Adjust the STUDS (I) so that the threads extend $\frac{3}{8}$ " below the CANOPY (S) and secure with HEX NUTS (I).
4. Attach the SAFETY CABLE (Y) to the brace or structure and secure using CABLE CLIP (Z).
5. Trim off the excess wire to a minimum 6" beyond the STEM (N) and strip each wire $\frac{1}{2}$ ".
6. Attach the Ground wire (Green) to the ground inside the outlet box (Generally green or bar copper wire). NEVER CONNECT GROUND WIRE TO "HOT" WIRE! FAILURE TO FOLLOW THIS COULD RESULT IN SERIOUS INJURY OR DEATH!
7. Connect the white fixture lead to the neutral (Generally white) wire in the outlet box. Fasten the wires together with an approved fastener (WIRE NUT) (G). Starting 1" below the fastener, tightly wrap the connection with electrical tape so that the connections seals the end of the fastener. MAKE SURE THERE ARE NO EXPOSED WIRE OF STRANDS THAT COULD CAUSE A DANGEROUS SHORT CIRCUIT!
8. Connect the black fixture leads to the hot (Generally black) wire in the outlet box. Fasten the joined wires same as previous step. NEVER REVERSE HOT AND NEUTRAL WIRES. FAILURE TO FOLLOW THIS COULD RESULT IN SERIOUS INJURY OR DEATH!
9. Push the wires back into the junction box. Lift up the CANOPY (S) up to the ceiling, and secure with the BALL NUTS (L).
10. Screw the BULB (P) onto the SOCKET of the FIXTURE ASSEMBLY (Q). THIS FIXTURE IS RATED FOR 25 WATT TYPE-A21 LAMP. DO NOT EXCEED THE RECOMMENDED WATTAGE!
11. Attach the CHAIN B (2) and CHAIN D (4) to the ACRYLIC PLATE (X) and secure using BARREL NUT (W).
12. Thread the NIPPLE (5) to CHAIN C (3) then attach the ACRYLIC PLATE (X) and secure using CHAIN A (1).
13. Thread the NIPPLE (V) TO CHAIN A (1) then attach it to the bottom end of GLASS (H) and secure HEX NUT (U).
14. Attach the GLASS (H) to the FIXTURE ASSEMBLY (Q) and secure with NYLON (R) using SCREW DRIVER (7). Attach the GLASS onto the FIXTURE ASSEMBLY (Q). (SEE GLASS ASSEMBLY PAGE).
15. Restore power to the OUTLET at the breaker or fuse box.


PART(S)	REPLACEMENT PART NAME	NUMBER
A,B,C,G,I,J,L	HARDWARE KIT	HDW-228-43
K,S,T	CANOPY ASSEMBLY	CAS-228-43
N	STEM	STM-TCI600-SET
H,R	GLASS ASSEMBLY	GAS-228-42
X	ACRYLIC PLATE	ACR-000228-43



PART(S)	REPLACEMENT PART NAME	NUMBER
IA	GLASS INSERT A	GAS-228-43-A
IB	GLASS INSERT B	GAS-228-43-B
IC	GLASS INSERT C	GAS-228-43-C
ID	GLASS INSERT D	GAS-228-43-D
IE	GLASS INSERT E	GAS-228-43-E
IF	GLASS INSERT F	GAS-228-43-F
IG	GLASS INSERT G	GAS-228-43-G
IH	GLASS INSERT H	GAS-228-43-H
II	GLASS INSERT I	GAS-228-43-I

FIXTURE INSTALLATION

1. Attach the GLASS INSERT (A,B,C,D,E,F,G,H,I) to the CHAIN of FIXTURE ASSEMBLY (Q) and secure with NYLON SCREW (6) using SCREW DRIVER (7).



GLASS ACCESSORIES PATTERN

