

PHILIPS

Home Access

Smart lever lock

2000 series

Philips Built-in WiFi Touchscreen Smart Lever Lock

DDL0M1020X-15HW

Integrated smart lever lock
Effortless access with multiple unlock methods



Specifications

Overview		Modes		Key Features	
Material	Aluminum alloy	Operation mode	Manual mode	Safety	Meets ANSI/BHMA standard
Color	Nickel / Matte black		Auto mode		AES128
Bolt type	Latch bolt		Passage mode		Local storage
Keyway	SC1	Security mode	Privacy mode	Alarms	Low battery alarm
Connectivity	Built-in Wi-Fi / Bluetooth				Wrong entry limit alarm
Unlock Methods		Power			Jam alarm
Unlocking from outside		Operating Environment		Remote control	App unlock
	PIN code / Home Access app / Key	Temperature	From -35 °C to 66 °C		Manage user accounts
Unlocking from inside	Lever	Humidity	0-93%		Create schedule PIN codes
	Home Access app	Installation Requirements			Simple sharing
	Voice assistant	Door thickness	1-3/8 to 2 inch (35-50mm)	Language	English / French / Spanish
Max Credentials Capacity		Opening direction	Left inside / Left outside	Voice navigation	Real person voice navigation
			Right inside / Right outside	Works with voice assistant	Amazon Alexa
Master PIN code	1	Cross bore hole	2-1/8 inch (54mm)		Google Assistant
User PIN code	100	Backset	2-3/8 or 2-3/4 inch (60mm/70mm)		
One-time PIN code	Unlimited				
Traditional key	2				



Fingerprint
unlock



PIN code
unlock



Integrated
lever



Traditional
key



Remote control
through app