



TEGERA® 8831R

Learn more

WARM AND SAFE WHEN IT'S DRY AND MOIST

Glove with cold protection in combination with high cut protection (Level D). Palm dipped in Latex, for dry and moist environments. 10 gg and CRF cut resistance technology. The glove is durable, soft and warm and the Latex-dipping provides a good grip. Perfect for all-round work in in cold and moist environments.

CHARACTERISTICS

- High level of protection
- Flexible
- Good grip
- Comfortable
- Warm

FUNCTIONS

- Withstands contact heat up to 250°C

CRF®

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF
Cut injuries, Scratches, lacerations, Contact with cold

PRIMARY ENVIRONMENTS OF USE
Cut risk environments, Cold environments, Moist environments

PRIMARY AREAS OF USE
Building and construction, Construction, Machine driving

PRIMARY INDUSTRIES OF USE
Agriculture, forestry and fishing, Facility management services, Basic metals manufacturing, Transportation and logistics, Building and construction, Mining and quarrying, Warehousing

TYPE OF WORK
Medium weight

SPECIFICATION
TYPE Cold insulation gloves, Cut resistant gloves, Heat protection gloves
CATEGORY Cat. II
LINING Winter-lined
KNITTING GAUGE (GG) 10
LINING MATERIAL Acrylic, CRF® Technology, HPPE, Polyester, Stainless steel fibre yarn
LENGTH 240-275mm
DEXTERITY 5
GRIP DESIGN Sandy finish
COLOUR Black
PAIRS PER: BUNDLE/CARTON 6/72
DISPLAY TYPE Hangtag with euro slot
DIPPING Palm-dipped
DIPPING MATERIAL Latex
CUFF STYLE Knitwrist cuff
CUFF MATERIAL Textile
CUT RESISTANCE (EN ISO 13997) Cut resistance level D
CUT RESISTANCE (EN ISO 13997) TDM: 22N
INNER MATERIAL SPECIFICATION Acrylic, HPPE (High performance polyethylene), Stainless steel fibre yarn, Polyester
OUTER MATERIAL SPECIFICATION Natural latex

COMPLIANCE
CE Cat. II
EAC TP TC 019:2011
EN ISO 21420:2020
EN 388:2016+A1:2018 1X42D
EN 407:2020 (No flame protection) X2XXXX
EN 511:2006 01X
ANSI A4 CUT
ANSI 4 ABR

Contact heat rating valid for palm area only

FEATURES
Cut protection
Warm lining

SIZE		ARTICLE NUMBER	EAN
7	S	8831R-7	7340118388434
8	M	8831R-8	7340118388649
9	L	8831R-9	7340118388793
10	XL	8831R-10	7340118388977
11	XXL	8831R-11	7340118389158
12	3XL	8831R-12	7340118408965

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.