

# Replacement AB DE-ION® Circuit Breakers

Types CA, CAH and HCA 225 Amperes

## Type CA, CAH and HCA Circuit Breakers

2 and 3 Poles, 240 VAC; Non-Interchangeable Trip

Listed with CSA and Underwriters Laboratories Inc. except as noted.

CSA and Underwriters Laboratories Inc. Listed Interrupting Ratings

Type CA: 100-225 Amperes, 10,000 AIC

Type CAH: 100-225 Amperes, 22,000 AIC

Type HCA: 100-225 Amperes, 42,000 AIC

## Breaker Catalogue Numbers

Continuous Ampere Rating at 40°C	Catalogue Number			
	Breaker Shipped with:			
	Line and Load Terminal Installed	Load Terminals Only Installed	Line Terminals Only Installed	No Terminals Installed

### Type: CA 10,000 Ampere I.C. Thermal-Magnetic Breakers

2-Pole, 240 VAC				
100	CA2100	CA2100X	CA2100Y	CA2100W
125	CA2125	CA2125X	CA2125Y	CA2125W
150	CA2150	CA2150X	CA2150Y	CA2150W
175	CA2175	CA2175X	CA2175Y	CA2175W
200	CA2200	CA2200X	CA2200Y	CA2200W
225	CA2225	CA2225X	CA2225Y	CA2225W
225 MCS	-	-	-	CA2225WK

3-Pole, 240 VAC				
100	CA3100	CA3100X	CA3100Y	CA3100W
125	CA3125	CA3125X	CA3125Y	CA3125W
150	CA3150	CA3150X	CA3150Y	CA3150W
175	CA3175	CA3175X	CA3175Y	CA3175W
200	CA3200	CA3200X	CA3200Y	CA3200W
225	CA3225	CA3225X	CA3225Y	CA3225W
225 MCS	-	-	-	CA3225WK

Type: CAH 22,000 Ampere I.C. Thermal-Magnetic Breakers				
2-Pole, 240 VAC				
100	CAH2100	CAH2100X	CAH2100Y	CAH2100W
125	CAH2125	CAH2125X	CAH2125Y	CAH2125W
150	CAH2150	CAH2150X	CAH2150Y	CAH2150W
175	CAH2175	CAH2175X	CAH2175Y	CAH2175W
200	CAH2200	CAH2200X	CAH2200Y	CAH2200W
225	CAH2225	CAH2225X	CAH2225Y	CAH2225W

3-Pole, 240 VAC				
100	CAH3100	CAH3100X	CAH3100Y	CAH3100W
125	CAH3125	CAH3125X	CAH3125Y	CAH3125W
150	CAH3150	CAH3150X	CAH3150Y	CAH3150W
175	CAH3175	CAH3175X	CAH3175Y	CAH3175W
200	CAH3200	CAH3200X	CAH3200Y	CAH3200W
225	CAH3225	CAH3225X	CAH3225Y	CAH3225W

Type: HCA 42,000 Ampere I.C. Thermal-Magnetic Breakers				
2-Pole, 240 VAC				
100	HCA2100	HCA2100X	HCA2100Y	HCA2100W
125	HCA2125	HCA2125X	HCA2125Y	HCA2125W
150	HCA2150	HCA2150X	HCA2150Y	HCA2150W
175	HCA2175	HCA2175X	HCA2175Y	HCA2175W
200	HCA2200	HCA2200X	HCA2200Y	HCA2200W
225	HCA2225	HCA2225X	HCA2225Y	HCA2225W

3-Pole, 240 VAC				
100	HCA3100	HCA3100X	HCA3100Y	HCA3100W
125	HCA3125	HCA3125X	HCA3125Y	HCA3125W
150	HCA3150	HCA3150X	HCA3150Y	HCA3150W
175	HCA3175	HCA3175X	HCA3175Y	HCA3175W
200	HCA3200	HCA3200X	HCA3200Y	HCA3200W
225	HCA3225	HCA3225X	HCA3225Y	HCA3225W



Type CA 3-Pole

## Accessories

Description	Catalogue Number
Handle Locks: Non-padlockable	CA23NPL
Handle Locks: Padlockable	CA23PL CA23LOCK
Mounting Hardware: Base mounting hardware – 2-pole	CA2BHW
Base mounting hardware – 3-pole	CA3BHW
Mounting BrACket – 2-pole	CA2MB
Mounting BrACket – 3-pole	CA3MB
Terminals: #3 to 300MCM	TA225CA2
2 & 3 Pole Collar Kit	177CS47G16

## Modifications

Description	Catalogue Suffix
Shunt Trip	S1 to S16
Auxiliary Switch	A1 to A16
Special Calibration (50°C)	V
Freeze Testing	H
Moisture-Fungus Treatment	F

Shaded gray areas denotes obsolete or discontinued products and services