Mona | E21344-GLD

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Whether used as vanity lighting or above portraits and shelves, the Mona wall sconces are sure to illuminate a masterpiece. The tubular LED frame rotates to direct the lighting wherever it is needed. The back plate is sized for single gang junction box installs and an additional cover plate is provided for convenience. Available in either a rich burnished Gold plated finish or Matte Black powder coat, these wall lights pair well in both modern and traditional settings.



MEASUREMENTS

DIMENSION	: 30.5" W x 4.25" H x 3" Ext
MAX OAH	: 3" W x 4.75" H
HANGING WEIGHT	: 3.52 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 1,260 Rated (900 Del.)
BULB	: 1 x 18W LED PCB Integrated , 18W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac CL or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Directional

FINISHES OPTION

Black (BK)
Gold (GLD)

MATERIAL

Aluminum, Acrylic, Steel

RATINGS

cETLus
Damp Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Horizontal
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com