
Cortex | E11060-144PC

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____







PRODUCT DESCRIPTION

A central, cylinder diffuser of opal white acrylic diffuses LED lighting within a cavity of thin ribbed glass of various lengths. Both imaginative and functional, the bright pendants encase an additional down light recessed within a Polished Chrome, Naturally Aged Brass or Matte Black housing casting light downward.

MEASUREMENTS

DIMENSION	: 4.75" W x 14.5" H x 2.5" Ext
MAX OAH	: 4.75" W x 4.75" H
HANGING WEIGHT	: 2.43 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 800 Rated (600 Del.)
BULB	: 1 x 10W LED PCB Integrated , 10W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)

Natural Aged Brass (NAB)

Polished Chrome (PC)

GLASS

Clear Ribbed 144

MATERIAL

Steel, Aluminum, Glass

RATINGS

cETLus
Damp Location
ADA

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com