Pipette | E31095-93PC

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Slender Clear glass tubes sheath a Polished Chrome rod that supports small LED lamps. The glass is etched at a dividing line in the glass to softly diffuse the light. Available in two lengths of glass tube, the pendants are also available in multiple configurations that create a modern candle-like cluster. The surface mounted option supports the glass on a structure that allows it to hang freely for dual purpose as a ceiling flush mount or a hanging glass shade when mounted to a wall. JA8 Listed LED G9 lamps are provided for efficient lighting and reduced energy consumption.



*max overall height

MEASUREMENTS

DIMENSION	: 11.75" L x 11.75" W x 18" H
MAX OAH	: 138" OAH
CANOPY	: 11.75" W x 1.4" H
HANGING WEIGHT	: 6.93 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 1,350 Rated (950 Del.)
BULB	: 3 x 4W LED G9 , 12W Total
BULB INCLUDED	: (Included)
DIMMABLE	: Y
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Polished Chrome (PC)

GLASS

Clear and Frosted 93

MATERIAL

Steel, Glass

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 25000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com